

STP High Performances IR Triggered Microchip Series



KEY FEATURES

- Ultra-short pulses down to 300ps
- Single-shot to 100kHz
- Multi-kW peak power
- Excellent beam quality
- Efficient, air-cooled
- Sealed package, extremely long life

For generating high peak power pulses of a few hundred picoseconds, microchip lasers are economical, compact, and reliable, within a sealed package ensuring incredibly long lifetime even in harsh industrial environment.

The triggered series offer the highest peak power and shortest pulses of the entire Microchip family. With these devices, the user is able to trigger pulse emission on demand from single-shot to 100kHz with the STP-100F.

APPLICATIONS

- Instrumentation
 - Ranging
 - Differential absorption LIDAR
 - Super-continuum generation
 - Distributed temperature sensing
 - Raman spectroscopy

- Biophotonics
 - Micro-dissection of cells
 - Brain nanosurgery
 - Protein cross-linking

All information contained herein is believed to be accurate and is subject to change without notice. Teem Photonics may not be held liable for its use. Teem Photonics, its subsidiaries and affiliates, reserve the right to modify or withdraw, at any time and without any notice, specifications, product design, product component. Some options may not be available for all products. Please contact Teem Photonics for details. August 18



TECHNICAL SPECIFICATIONS

New! Preliminary specs		New! Preliminary specs	New!	
	STP-40K-1x0	STP-07E-1x0	STP-10E-1x0	STP-100F-1x0
Wavelength	1064nm	1064nm	1064nm	1064 nm
Maximum Repetition Rate RR _{max} ⁽¹⁾	500Hz	4 kHz	4.5 kHz	100 kHz
Constant Pulse width (FWHM) ⁽²⁾	[0.3;0.4]ns	<0.7ns	>8ns	<0.75 ns
Output Energy	>12 µJ	>7 µJ	≥14 µJ	>0.75 µJ
Peak Power	>30kW	>10kW	>1kW	>1kW
PCD ⁽³⁾	<160µs	<70µs	<100µs	<70µs
PCD jitter	<±1.5µs	<±1.5µs	<±1.5µs	<±1.5µs
Short term (1min) power stability ⁽⁴⁾	<±1%	<±1%	<±1%	<±2%
Long term (6 hrs) power stability ⁽⁴⁾	<±3%	<±3%	<±3%	<±5%
Spectral properties	Single Longitudinal Mode	Single Longitudinal Mode	Single Longitudinal Mode	Single Longitudinal Mode
Beam profile	Gaussian TEM00	Gaussian TEM00	Gaussian TEM00	Gaussian TEM00
Full angle divergence Horizontal@1/e ² Vertical@1/e ²	15±2mrad 15±2mrad	13±5mrad 13±5mrad	4.3±0.5mrad 4.3±0.5mrad	10±2mrad 9±2mrad
M ²⁽⁵⁾	<1.3	<1.3	<1.2	<1.3
Beam ellipticity ⁽⁶⁾	<1.1	<1.3	<1.2	<1.3
Main Lobe Gaussian Fit ⁽⁷⁾	N/A	N/A	N/A	N/A
Polarization	Linear PER>20dB	Linear PER>20dB	Linear PER>20dB	Linear PER>20dB
Package dimensions Package weight	144x42x36mm 300g	144x42x36mm 300g	144x42x36mm 300g	144x42x36mm 300g
Options	Ū	Ū	Ū	Ũ
(table p3)	0,1,2,3,4,F,M	0,1,2,3,4,F,M	0,1,2,F,M	0,1,2,3,F,M
Options included	S	S	S	S

NOTES

(1) See options p3

- (2) Measured with 1Ghz photodiode and 1GHz/10GS/s oscilloscope.
- (3) PCD = Pulse Creation Delay, the delay between the trigger command and the effective pulse firing
- (4) For temperature variation < ± 3°C and < 3°C/hour, stability is measured with calorimeter detector band [DC, 2Hz]
- (5) Mean average value M = $\sqrt{(XY)}$, X and Y being respectively the major and minor axis of the ellipse
- (6) Beam ellipticity is calculated as the ratio of the main axis far field divergence (7) Measurement performed in the far field with a WincamTD-U series camera

All information contained herein is believed to be accurate and is subject to change without notice. Teem Photonics may not be held liable for its use. Teem Photonics, its subsidiaries and affiliates, reserve the right to modify or withdraw, at any time and without any notice, specifications, product design, product component. Some options may not be available for all products. Please contact Teem Photonics for details. August 18



COMPLEMENTARY INFORMATION & OPTIONS

Environment Parameters					
Operating Temperature Range	0-50°C; 15-35°C for STP-10E-1x0				
Maximum Laser Head Baseplate Temperature	50°C				
Maximum Power Consumption	<40W				
Laser Head Thermal Dissipation	<15W				
Storage Temperature	0-50°C				
Shock of 11ms according to IEC 68-2-27, non operating	25g				
Vibration 5Hz to 500Hz sinusoidal according to IEC 68-2-6	2g				


Certification					
Laser classification according to IEC 60825-1:2007	3В				
CDRH	Yes, if used with a MLC-03A-DP1 or -DP2 controller				
ROHs	Yes				

Options				
Fixed Repetition Rate = RR _{max}	-10x version			
Fixed Repetition Rate ≠ RR _{max}	-11x version ; RR to be chosen over 10Hz-RR _{max}			
External Variable Repetition Rate	-12x version ; single shot to RR _{max} , 1 optimized RR value; exception for the STP-100F-1x0 laser: tunability possible in the [RR-10%;RR] range only			
External Variable Multi-Repetition Rate	-13x version ; single shot to RR _{max} , 3 optimized RR values; exception for the STP-100F-1x0 laser: tunability possible in the [RR-10%;RR] range only for each RR			
External Continuous Variable Repetition Rate	-14x version ; optimized over [10Hz-RRmax] if RRmax ≤ 2kHz; or [10Hz - 2kHz] if RRmax > 2kHz; <i>not available for the STP-</i> 100F-1x0			
Multimode fibering (M)	Contact factory for availability			
Single mode fibering (F)	Contact factory for availability			
Collimation (C)	Contact factory for availability			
Synchronization output (S)	TTL compatible output signal for synchronization/monitoring			

Available Controller Types							
Model for the STP-100F-1x0	Model for the other STP lasers	Туре	Input Power	CDRH			
MLC-03A-DP2	MLC-03A-DP1	Desktop	100-240 V AC	Yes			
MLC-03A-MP2	MLC-03A-MP1	Module	12 V DC	No			
MLC-03A-BP2	MLC-03A-BP1	Board	12 V DC	No			



CDRH LASER HEAD MECHANICAL DRAWINGS: STP LASERS



All information contained herein is believed to be accurate and is subject to change without notice. Teem Photonics may not be held liable for its use. Teem Photonics, its subsidiaries and affiliates, reserve the right to modify or withdraw, at any time and without any notice, specifications, product design, product component. Some options may not be available for all products. Please contact Teem Photonics for details. August 18

www.teemphotonics.com

STx series I 4/4