
 **Bottle Top Dispenser**
FORTUNA® OPTIFIX® SOLVENT,
 with glass piston, FIX adaptor
 made of white PP, comes with
 2 PP adaptors GL 40+45,
 1 PTFE intake tube, single pack

 **Flaschenaufsatzdispenser**
FORTUNA® OPTIFIX® SOLVENT,
 mit Glaskolben, FIX Adapter
 aus weißem PP, inkl.
 2 PP-Adapter GL 40+45,
 1 PTFE-Ansaugschlauch, VE 1





ISO 8655

Volume Volumen	grad. grad.	Accuracy Richtigkeit	Tolerance Toleranz	Art.-No. Art.-Nr.
0.4 - 2 ml	0.1 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-27
1 - 5 ml	0.1 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-33
2 - 10 ml	0.2 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-38
6 - 30 ml	0.5 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-44
10 - 50 ml	1.0 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-48
20 - 100 ml	2.0 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-51
40 - 200 ml	5.0 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-53
60 - 300 ml*	5.0 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-56
100 - 500 ml*	5.0 ml	$\leq \pm 0.6 \%$	$\leq \pm 0.2 \%$	101.081-58

* additional to ISO 8655

* in Ergänzung zur ISO 8655

 **For dispensing solvents**
 **Zur Dosierung von Lösungsmitteln**